Crimp insert - CRIMPFOX-M SC 2,5/DIE

1212084

https://www.phoenixcontact.com/us/products/1212084

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Die, for Crimpfox-M, for non-insulated slip-on sleeves 0.5 - 2.5 mm^2

Commercial Data

Item number	1212084
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	B14
Product Key	BH313Y
Catalog Page	Page 436 (C-3-2019)
GTIN	4046356454544
Weight per Piece (including packing)	73.9 g
Weight per Piece (excluding packing)	73.9 g
Customs tariff number	82032000
Country of origin	SE

Technical Data

Product properties

Product type	Die
Compression	B crimp

Crimping position 1

Min. cross section	0.5 mm²
Max. cross section	1 mm²
AWG min	22
AWG max	16

Crimping position 2

Min. cross section	1.5 mm²
Max. cross section	2.5 mm²
AWG min	16
AWG max	14

Connection data

Conductor connection

Cross section range, metric	0.5 mm² ... 2.5 mm²

Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

Material specifications

Color	black

Approvals

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-9.0	21019290
ECLASS-10.0.1	21019290
ECLASS-11.0	21049090

ETIM

ETIM 8.0	EC011823

UNSPSC

UNSPSC 21.0	27111500

Phoenix Contact 2022 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com