



Our commitment. Your advantage.



• [Products](#)

- [By Type](#)
 - [Connectors](#)
 - [Electromechanical Components](#)
 - [Electronic Modules](#)
 - [Fiber Optics](#)
 - [Filters](#)
 - [Identification & Labeling](#)
 - [Passive Components](#)
 - [Power Sources](#)
 - [RF & Microwave Products](#)
 - [Tooling Products](#)
 - [Touch Screen Displays](#)
 - [Tubing, Molded and Harnessing Products](#)
 - [Wire, Cable and Cable Assemblies](#)
 - [List all product types...](#)
- [By Industry](#)
 - [Aerospace & Defense Products](#)
 - [Appliance](#)
 - [Automotive](#)
 - [Communications](#)
 - [Computer & Consumer Electronics](#)
 - [Industrial & Commercial](#)
 - [Instrumentation & Medical](#)
- [By Brand](#)
- [A to Z](#)
- [Product Innovations](#)

• [Documentation](#)

- [Find Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

• [Resources](#)

- [RoHS Compliance & Alternates](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

• [My Account](#)


- [Manage My Part Lists](#)
- [Manage My Downloads](#)
- [Sign In](#)
- [Register](#)

• [Customer Support](#)

- [Support](#)
- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [Subscribe to Newsletter](#)

205432-2 Product Details





205432-2
T E Part Number: 205432-2
 **Active**
 [Add to Part List](#)

Subminiature D Pin/Socket Connectors for MIL-C-24308 and MIL-C-39029

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- Connector
- Product Series = 109
- Density = Standard
- Term inate To Wire
- Number of Positions = 50

[View all Features](#) | [Find Sim ilar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)
- [Request Samples](#) **NEW!**

Documentation & Additional Information

Product Drawings:

- [KIT, "HDM" SERIES RECEPTACLE, SIZE #5](#) (PDF, English)

Catalog Pages/Data Sheets:

- [AEROSPACE & DEFENSE](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insert Arrangement](#)

Related Products:

- [Tooling](#)

[List all Docum ents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 109
- [Number of Positions](#) = 50
- [Gender](#) = Receptacle
- [Shell Size](#) = 5
- [Shell Material](#) = Steel
- [Wire Termination Type](#) = Crimp
- Mounting Hole Diam eter (m m [in]) = 3.05 [.120]
- Comment = Size 20 contacts supplied with connectors are loose piece.

Body Related Features:

- [Blindm ate](#) = No
- [Non-Magnetic](#) = No
- [Sockets](#) = With
- [Rear Grom met](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Cadm ium
- Mount Style = Floating Bushing
- Retention Clip Material = Stainless Steel

Contact Related Features:

- [Contact Size](#) = 20
- [Contact Style](#) = Crimp Snap-in

Configuration Related Features:

- [Density](#) = Standard

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M24308/2-27F
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- NASA Qualification = No

Conditions for Usage:

- Term inate To = Wire

Other:

- Brand = AMP