Search Results

Evaluate
- FAQ's

Design a Solution
- Part Drawings
- PDF Fiber Optic..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'F9LD3-3M4'**

Your search criteria matched only one product, shown below

F9LD3-3M4



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F9LD3-3M4
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	SC to SC singlemode duplex patch cord, 3mm jacketed cable (two SC connectors on each end) – 9/125?m.
Product Type	SC Patch Cords
Length (m)	4
Fiber Compatibility	9/125?m
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Cable Color	Yellow
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	SC Connector
Connector 2 Type	SC Connector
End Configurations	SC to SC
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	SC-SC LSZH 9µ m Dupl 3mm Patch Cord 4m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy