








1. CODING VARIANT
2. APPLICATION TEMP. -40°C ~140°C

1-2394085-3	M	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	M	PA66-GF	AQUA RED		1	1
1-2394085-2	L	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	L	PA66-GF	AQUA BROWN		1	1
1-2394085-1	K	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	K	PA66-GF	AQUA GREEN		1	1
2394085-9	J	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	J	PA66-GF	ORANGE		1	1
2394085-8	H	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	H	PA66-GF	YELLOW		1	1
2394085-7	G	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	G	PA66-GF	RED		1	1
2394085-6	F	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	F	PA66-GF	BROWN		1	1
2394085-5	E	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	E	PA66-GF	GREEN		1	1
2394085-4	D	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	D	PA66-GF	PURPLE		1	1
2394085-3	C	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	C	PA66-GF	BLUE		1	1
2394085-2	B	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	B	PA66-GF	NATURE		1	1
2394085-1	A	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	PLUG HOUSING	-	PA66-GF	ORNGE	(33)	1	7
			SHIELDING	-	COPPER ALLOY	Ag PLATED		1	6
			CPA - FINGER ACCESS	-	PA66-GF	RED		1	5
			CPA SPRING - FINGER ACCESS	-	STAINLESS STEEL	-		1	4
			HVIL	-	COPPER	Ag PLATED		1	3
			PERIPHERAL SEAL	-	SILICION	-		1	2
			PLUG TPA	A	PA66-GF	BLACK		1	1
TE ASSY NO.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM




FOR FINGER ACCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P.LING	26AUG2021	 TE Connectivity	
			CHK J.L.I	26AUG2021		
DIMENSIONS:						



- 1 CODING VARIANT
2. APPLICATION TEMP. -40°C ~140°C

3-2394085-3	M	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	M	PA66-GF	AQUA RED	(33)	-	2-7
									1	1
3-2394085-2	L	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	L	PA66-GF	AQUA BROWN	(33)	-	2-7
									1	1
3-2394085-1	K	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	K	PA66-GF	AQUA GREEN	(33)	-	2-7
									1	1
2-2394085-9	J	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	J	PA66-GF	ORANGE	(33)	-	2-7
									1	1
2-2394085-8	H	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	H	PA66-GF	YELLOW	(33)	-	2-7
									1	1
2-2394085-7	G	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	G	PA66-GF	RED	(33)	-	2-7
									1	1
2-2394085-6	F	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	F	PA66-GF	BROWN	(33)	-	2-7
									1	1
2-2394085-5	E	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	E	PA66-GF	GREEN	(33)	-	2-7
									1	1
2-2394085-4	D	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	D	PA66-GF	PURPLE	(33)	-	2-7
									1	1
2-2394085-3	C	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	C	PA66-GF	BLUE	(33)	-	2-7
									1	1
2-2394085-2	B	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	B	PA66-GF	NATURE	(33)	-	2-7
									1	1
2-2394085-1	A	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	PLUG HOUSING	-		PA66-GF	ORNGE	(33)	1	7
			STAINLESS STEEL	-		COPPER	Ag PLATED		1	6
			CPA - TOOL ACCESS	-		PA66-GF	RED		1	5
			CPA SPRING - TOOL ACCESS	-		STEEL	-		1	4
			HVIL	-		COPPER	Ag PLATED		1	3
			PERIPHERAL SEAL	-		SILICION	-		1	2
			PLUG TPA	A		PA66-GF	BLACK		1	1
TE ASSY NO.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM	



FOR TOOL ACCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN	26AUG2021	TE Connectivity	
DIMENSIONS:		CHK	26AUG2021		
mm		J.L.I	26AUG2021		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		±0.5		PLUG ASSEMBLY	
		7-PLC ±0.1		HVP-HD1000	
		1-PLC ±0.1		SIZE	
MATERIAL		2-PLC ±0.01		CAGE CODE	
		3-PLC ±0.001		DRAWING NO	
		4-PLC ±0.0001		116-160182	
		FINISH		RESTRICTED TO	
		WEIGHT		A 00779	
		CUSTOMER DRAWING		SCALE 2:1	
				SHEET 2 OF 3	
				REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

