Search Results

Evaluate
- FAQ's
- Product Bulletins
- PDF-Metal Detect..

Design a Solution
- Part Drawings
- PDF-Metal Detect..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'TM2S8-C86'**

Your search criteria matched only one product, shown below

TM2S8-C86

- Cradle design holds cables securely in place; provides maximum stability for cable bundle
- Low profile design keeps bundle close to mounting surface
- Available in nylon 6.6 material for general purpose applications
- Available in polypropylene material which provides superior resistance to harsh cleaning chemicals
- Both materials are available in separate but distinct blue colors to facilitate visual detection
- For indoor use

Part Number	TM2S8-C86
RoHS Compliancy Status	Compliant
Part Description	Cable Tie Mount, Nylon Metal Detectable, Light Blue
Product Type	Cable Tie Mounts- Screw / Rivet Mounted
Material	Metal Impregnated Nylon 6.6
Color	Light Blue
UL Recognized	No
Height (In.)	0.275
Height (mm)	7.0
Length (In.)	0.42
Length (mm)	10.7
Width (In.)	0.630
Width (mm)	16.0
CE Compliant	No
Environment	Indoors
Material Flammability Rating	HB
Mounting Method	#8 (M4) Screw
Pricing Description	Cable Tie Mount, Metal Detectable Nylon, Light Blue
Screw Size	#8
Screw Size Metric	M4
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy