
Pomona®

DIP Clips® for 8-14-16-20-24-40 Pin Clips And 8 Through 40 Pin DIP Removers

Pomona DIP Clip® test clips are designed for testing dual-in-line IC packages on PC boards. These devices incorporate many built-in features that assure a positive electrical connection as well as hands free testing.



- Contacts (.040" wide on lower end) are serrated for the best electrical contact.
- .025" X .028" serrated test points on upper end will accept wire wraps or mini test clips.
- Molded barriers between contacts allows live board connections without accidental shorting of contacts.
- Can also be used as an insertion tool for DIPs.
- Contacts are spring tempered Nickel Silver or Gold Plated Beryllium Copper alloy. Oxide penetrating clips have a roughened stainless steel surface treatment.
- Open back option allows probing on the chip leads while clip is attached.

Pomona's DIP Clip® test clips are perfect for emulation, field service, failure analysis, and for use with logic analyzers.

Size Pins	Clip Width	**Standard DIP Clip®**	**Open Back DIP Clip®**	**Contact Material and Plating**	**Oxide Penetrating DIP Clip®**	**Static Control DIP Remover**
8	.43	**5108**	**5208**	Be-Cu, Gold Plate	**5649**	**5016**
14	.72	**5014**	**5114**	Nickel Silver	**5650**	**5016**
		5214	**5314**	Be-Cu, Gold Plate	**5650**	**5016**
16	.83	**3916A**	**4236A**	Nickel Silver	**5692**	**5016**
		5116	**5216**	Be-Cu, Gold Plate	**5692**	**5016**
20	1.03	**5120**	**5220**	Be-Cu, Gold Plate	**5693**	**5016**
24	1.22	**4124A**	**4324A**	Nickel Silver	**5694**	**5024**
		5124	**5224**	Be-Cu, Gold Plate	**5694**	**5024**
40	2.02	**4140A**	**4340A**	Nickel Silver	**5695**	**5040**
		5140	**5240**	Be-Cu, Gold Plate	**5695**	**5040**


All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (,51 mm), .xxx = ± .005" (,127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 909-469-2900 Fax: 909-629-3317
Technical Assistance: 800-241-2060

Pomona*ACCESS* **90220** (800) 444-6785 or (949) 253-3858
More drawings available at www.pomonaelectronics.com

Pomona®

DIP Clips® for 8-14-16-20-24-40 Pin Clips And 8 Through 40 Pin DIP Removers



FEATURES:

- For use with 14 or 16 Dual-In-Line I.C. packages.

MATERIALS:

Insulation: Glass filled nylon. Color: Red.
Hinge Pin: Stainless steel 302, passivated per QQ-P-35.

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

ORDERING INFORMATION: Model 4386

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (,51 mm), .xxx = ± .005" (,127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 909-469-2900 Fax: 909-629-3317
Technical Assistance: 800-241-2060