Catalog

Swage Standoffs

Model: 3073-B-440-B

Select Finish

-0 No Plate

Select Finish

-0 No Plate

RFQ

Choose a CAD format | Download CAD

View 3D Model | View 2D Drawing | View Spec Sheet

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 4-40 and length is 1-7/8".

SWAGE TOOLING		
±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

RAF_catalog_0097.pdf

Thread	4-40
O.D.	1/4"
Shape	Round
Length (L)	1-7/8"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate