DATE	REV	ECN	APP'D. BY
08/12/20	A0	–	JME
08/27/20	A1	11600	BTS



⚠3 CONTACTS	0.1/10	0.1/10	0.1/28
3.5 3p stereo plug	1	2	3
3.5 3p stereo plug	1	2	3

P/N STRUCTURE

BC–A3YYXXXF

- UNITS: F = FEET
- LENGTH: 003 = 3.0
- END #2: M = MALE
- END #1: M = MALE
- CONNECTOR TYPE: 3 = 3 PIN STEREO
- CODE: A = AUDIO
- FAMILY

NOTES:

1. CABLE: 28 AWG CONDUCTOR WIRE (x2), 0.10 CCS (x28); PVC JACKET, BLACK
2. CONNECTORS: ø 3.5 MM 3 PIN STEREO PLUG (2 MALE)

⚠3 CONTACTS: COPPER ALLOY



BC–A3MMXXXF

PART NUMBER

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1

RoHS

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
http://www.belfuse.com

TITLE: 3.5 MM AUDIO CABLE (MALE TO MALE)

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/

DRN BY: BTS	DATE 08/12/20		
APPD BY: JME	DATE 08/12/20		
DWG NO. CT999219		REV. A1	

AutoCAD