Blackburn®

T&B Catalog Number: **ADR25**
UPC Number: 78378661010
Description: Type ADR-ALCUL Single-Conductor, One-Hole Mount for Conductor Range Max 250 kcmil, Min 6 Str.

Status: Active



Features	
-	Easy Installation - no special tools required.
General	
-Style	ALCUL Single-Conductor, One-Hole Mount
-Material	Aluminum
-Plating	Tin-Plated
-Conductor Range (AL or CU) Maximum	250 kcmil
-Conductor Range (AL or CU) Minimum	6 Str.
Dimension Information	
-Length (inches)	2
-Width (inches)	1
-Height (inches)	1 1/8
-D (inches)	15/32
-E (inches)	5/16
-F (inches)	1/4
-G (inches)	1
Packaging	
-T&B Inner Pack	25
-Package in Units	250
-T&B Sold in UOM	Each
-T&B Weight Per UOM	11.76 lbs. per 100
Application Support	
-T&B Sales Drawings	wsd-000391
Notes	
-	5/16 Socket screw on sizes 250 through 350 kcmil.
-	UL 486B tested, AL9CU rated
Certifications	
-RoHS Compliance	Yes

Certifications

File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com