Specification Sheet

Part Number: 151-15800

Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable

Releasable for easy access to cables when necessary

Available in adhesive or screw-mount versions

Article Number	151-15800
Type	FKH80A
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary. These clamps are available in adhesive or screw mount versions.
Short Description	Flat Ribbon Cable Clamp, Adhesive, 3.38'' Hole Dia, PA66HIR, Black, 100/pkg

Global Part Name	FKH80A-PA66HIR-BK
Length L (Imperial)	3.38
Length L (Metric)	86.0
Fixation Method	Adhesive
Variant	Mounting clip
Width W (Imperial)	0.98
Width W (Metric)	25.0
Mounting Hole Diameter D (Imperial)	0.122 "
Mounting Hole Diameter D (Metric)	3.1 mm
Mounting Hole Diameter D Max (Metric)	3.1
Material	Polyamide 6.6, high impact modified (PA66HIR)
Material Shortcut	PA66HIR
Adhesive	Acrylate with base of polyurethane foam
Flammability	UL 94 HB (excluding adhesive)
UV Resistant (Yes/No)	No

Adhesive Operating Temperature	to +221°F (+105°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.