Specification Sheet

Part Number: CTN20STD



Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture.
Tubing protects cables and wires against automotive fluids and vibration wear.

Weather resistant material provides protection against water, snow, ice, and the effects of heat or cold.

Nylon material is formulated to withstand high temperatures.

Lateral slit allows fast and easy insertion of wires.

Convoluted Tubing, Slit, 2" Dia, PA6, Black with Gray Stripe, 100 ft/pkg

Article Number	169-60011
Type	CTN20
Color	Black with Gray Stripe (BKSTGY)
Quantity Per	carton
Product Description	Convoluted tubing provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It also can serve to protect valuable wiring circuits. HellermannTyton's convoluted tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat or cold on cables and wires. Available in standard, bulk, and dispenser box packaging. Material is slit.

Short Description	Convoluted Tubing, Slit, 2" Dia, PA6, Black with Gray Stripe, 100 ft/pkg
Global Part Name	CTN20-PA6-BK
Technical Description	Convoluted Tubing, Slit, 2" Dia., PA6, Black w/Gray Stripe
Length L (Imperial)	100.0
Length L (Metric)	30.5
Variant	Slit
Inner Diameter D (Imperial)	2.038
Inner Diameter D (Metric)	51.77
Diameter D (Imperial)	2.388
Diameter D (Metric)	60.66
Outside Diameter OD (Imperial)	2.388
Outside Diameter OD (Metric)	60.66
Nominal Diameter (Imperial)	2
Nominal Diameter (Metric)	50.8
Wall Thickness WT (Imperial)	0.011

Wall Thickness WT (Metric)	0.28
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Flammability	UL 94 HB
Halogen Free	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.