Part Number: 1300980182

Status: Active

Overview: Strain-Relief Cord Grips

Description: MAX-LOC Strain Relief Cord-Sealing Grip,1-1/4" NPT, Straight Male Cable Diameter 31.75-34.42mm (1.250-1.355")

Series image - Reference only

Documents:
RoHS Certificate of Compliance (PDF)
Product Literature (PDF)

Agency Certification

CSA	LR32159
UL	E76954

General

Product Family	Cable Grips
Series	130098
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872141
Use With	1 1/4" NPT Lock-Nut 1300990146

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	31.75-34.42mm (1.250-1.355")
Color - Grommet	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	65.650/g
Number of Holes	1
Thread Size	1 1/4" NPT

Material Info

Engineering Number	5576

EU ELV
Not Relevant

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130098 Series