Part Number: 1301470078
Status: Active
Overview: Watertite Wet-Location Wiring Solutions
Description: Watertite Plug with Locking Blade, 3 Pole/4 Wire, NEMA L14-30, 125V/250V, Cord Grip Body Size F4, Black

Series image - Reference only

Documents:
RoHS Certificate of Compliance (PDF) Product Literature (PDF)

Agency Certification

CSA	LR6837
UL	E10176

General

Product Family	Wiring Devices
Series	130147
Comments	125V and 250V, 125V and 250V
Exclude SD Check	Yes
IP Rating	IP67
NEMA Configuration	NEMA L14-30
Overview	Watertite Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite
Receptacle Type	N/A
Specialty	N/A
Type	Plug
UPC	78678871386

Physical

Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Locking Blade	Yes
Poles	3-pole/4-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V

Material Info

Engineering Number	28W74BLK

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130147 Series