

1337812-1 Product Details

Have a Question?

Chat with a Product Information Specialist



1337812-1

TE Internal Number: 1337812-1

 [Active](#)

RF Coax Cable Assemblies

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)




Product Highlights:

- 2 Connectorized Ends
- RF Coax Cable Assemblies Application
- Connector Type = SMA Right Angle Plug to SMA Right Angle Plug
- Assembly Length = .25 M
- Coaxial Cable Type (RG/U or Mfg.) = 316

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Connector Type](#) = SMA Right Angle Plug to SMA Right Angle Plug

Electrical Characteristics:

- Connector Impedance (Ω) = 50

Body Related Features:

- [Number of Connectorized Ends](#) = 2
- [Assembly Length \(M \[ft\]\)](#) = 0.25 [0.820]
- [Body Plating](#) = Stainless Steel

Contact Related Features:

- Center Contact Plating = Gold

Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 316

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Operation/Application:

- Application = RF Coax Cable Assemblies

Other:

- Brand = Greenpar

 [BOOKMARK](#) 

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address



Follow us on:

