

2057353-1 Product Details

[Share](#) | [Print](#) | [Email](#)


2057353-1

TE Internal Number: 2057353-1

Active

[View 3D PDF](#)

Pluggable Connectors, Cages & Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- SFP+ Enhanced Application
- Cage
- Cage Type = Ganged
- EMI Containment = Elastomeric Gasket
- Heat Sink Application = No

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • SFP+ ENHANCED 1X4 CAGE ASSEMBLY, PRESS-FIT (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • Single Port SFP+ Cages, Ganged SFP+ Cages, and SFP+ ... (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • Small Form-Factor Pluggable (SFP) and SFP+ Surface Mo... (PDF, English) <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Cage • Termination Type = Press-Fit <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Configuration = 1 x 4 • PCB Mount = Single Sided <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Post Length (mm [in]) = 2.05 [0.081] <p>Dimensions:</p> <ul style="list-style-type: none"> • Height (mm [in]) = 9.70 [0.382] <p>Body Features:</p> <ul style="list-style-type: none"> • Length (mm [in]) = 48.70 [1.917] • Width (mm [in]) = 57.25 [2.254] <p>Housing Features:</p> <ul style="list-style-type: none"> • Cage Type = Ganged • Cage Material = Nickel Silver 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • EMI Containment = Elastomeric Gasket • Lightpipe = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = SFP+ Enhanced • Heat Sink Application = No <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Box <p>Other:</p> <ul style="list-style-type: none"> • Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

