


2198230-1 Product Details

Share | Print | Email



2198230-1

TE Internal Number: 2198230-1

Preliminary

View 3D PDF

Pluggable Connectors, Cages & Accessories

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- SFP+ Enhanced Application
- Cage
- Cage Type = Ganged
- EMI Containment = External Springs
- Heat Sink Application = Yes

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI SPRI... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version 1) • 3D Model (IGES, Version 1) • 3D Model (STEP, Version 1) 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Cage • Termination Type = Press-Fit <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Configuration = 1 x 2 • PCB Mount = Double Sided (Belly-to-Belly) <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Heat Sink Type = PCI <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Post Length (mm [in]) = 2.05 [0.081] <p>Dimensions:</p> <ul style="list-style-type: none"> • Height (mm [in]) = 13.20 [0.520] <p>Body Features:</p> <ul style="list-style-type: none"> • Length (mm [in]) = 48.70 [1.917] • Width (mm [in]) = 28.75 [1.132] 	<p>Housing Features:</p> <ul style="list-style-type: none"> • Cage Type = Ganged • Cage Material = Nickel Silver <p>Configuration Features:</p> <ul style="list-style-type: none"> • EMI Containment = External Springs • Lightpipe = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = Not reviewed for ELV/RoHS compliance • Lead Free Solder Processes = Not reviewed for lead free solder process <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = SFP+ Enhanced • Heat Sink Application = Yes <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Tray <p>Other:</p> <ul style="list-style-type: none"> • Brand = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

