



What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Terminals & Splices > Product Feature Selector > Product Details

Share Print Email

### 35773 Product Details



35773

TE Internal Number: 35773

Active

View 3D PDF

#### Ring and Spade Tongue Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

##### Product Highlights:

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = SOLISTRAND
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

View all Features

##### Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

#### Documentation & Additional Information

##### Product Drawings:

- TERMINAL, SOLISTRAND, RING TONGUE, WIRE SIZE: 12-10 (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version D)
- 3D Model (IGES, Version D)
- 3D Model (STEP, Version D)

##### Related Products:

- Tooling

List all Documents

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire
- Insulation = No
- Insulation Support = Non-Insulation Support
- Stud Diameter (mm [in]) = 8.30 [0.327]
- Stud Size = 5/16 [M8]
- Shape = RING-048
- Heavy Duty = No
- Finish = Tin

##### Body Features:

- Body Style = SOLISTRAND
- Wire Range (mm [AWG]) = 3.00-6.00<sup>2</sup> [12-10]
- Material = Copper
- Stock Thickness (mm [in]) = 0.99 [0.039]

##### Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Packaging Features:

- Packaging Method = Loose Piece

##### Other:

- Brand = AMP

#### Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

#### Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

#### Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

