


1609012-3 Product Details

 **Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri


1609012-3

TE Part Number: 1609012-3

 **Active**
 [Add to Part List](#)

EMI/RFI Filters and Accessories

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- Filter - EMI/RFI
- Filter Type = Power Line
- H (3-15 Amp) Series
- Medical Application
- Mount Style = Flange

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insertion Loss/Specifications](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Filter - EMI/RFI
- [Filter Type](#) = Power Line
- [Filtered](#) = Yes

Electrical Characteristics:

- [Current Rating \(Amps.\)](#) = 6
- [Voltage ≤ \(VAC\)](#) = 250
- Leakage Current (Line-to-Ground) Max. @ 120 VAC 60 Hz (μA) = 2
- Leakage Current (Line-to-Ground) Max. @ 250 VAC 50 Hz (μA) = 5

Termination Related Features:

- [Terminal Input - Output Combination](#) = 1/4" Faston - 1/4" Faston

Body Related Features:

- [Series](#) = H (3-15 Amp)
- [Mount Style](#) = Flange
- Terminal Style Output = Straight

Contact Related Features:

- Approved Standards = UL Recognized, VDE Approved, CSA Certified

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Need Min Size With IEC Connector = No
- Need Optional Switch, Fusing, Or Voltage Selector = No

Operation/Application:

- [Application](#) = Medical

Other:

- Ground Choke Option = Without
- Brand = Corcom
- [Ground Option](#) = None
- Facility Installation = No