



+ CONNECTORS

BOARD-TO-BOARD CONNECTOR CONTACTS



✓ Active

TE CONNECTIVITY (TE)
2MM HM CABLE REC CONT FORM

Z-PACK | Z-PACK 2mm HM

1376260-2
TE Internal Number: 1376260-2

EU RoHS Compliant
EU ELV Compliant

Contact Type Receptacle, Socket
Contact Mating Area Plating Material Gold
Wire Range .05 – .12 mm² [30 – 26 AWG]
PCB Mount Retention Without
Body Style Straight

↓ **PRODUCT DRAWING**
Japanese

↓ **3D PDF**

DOCUMENTATION

Product Drawings

RECEPTACLE CONTACT AMP MCC CONN

PDF (TIFF AVAILABLE)

Japanese

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Crimping Of AMP METRIC CRIMP CABLE (MCC)

PDF

Japanese

Crimping Of AMP METRIC CRIMP CABLE (MCC)

TIF

Japanese

Product Specification

AMP-Metric Crimp Cable Connector

TIF

English

AMP-Metric Crimp Cable Connector

PDF

English

Application Specification For 2.0mm,2.5mm Pitch WTB CONNECTOR

TIF

Japanese

Application Specification For 2.0mm,2.5mm Pitch WTB CONNECTOR

PDF

Japanese

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable

Product Type Contact

With Insulation Support Yes

Make First / Break Last No

Type MCC

Body Features

Body Style Straight

Contact Features

Contact Type Receptacle, Socket
Contact Mating Area Plating Material Gold
Contact Current Rating (Max) (A) 1
Contact Mating Area Plating Thickness .762 μm [30 μin]
Contact Style High Current
Contact Base Material Phosphor Bronze

Termination Features

Termination End Plating Thickness .76 μm [30 μin]
Termination End Plating Material Gold
Interface Type 2mm HM

Mechanical Attachment

PCB Mount Retention Without

Dimensions

Wire Range .05 – .12 mm² [30 – 26 AWG]

Usage Conditions

Operating Temperature Range (°C) -20 – 85

Operation/Application

For Use With Cable Connectors

Packaging Features

Packaging Method Reel
Packaging Quantity 15000

Other

Comment For Applicator

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance

PDF