


1 - 86427 - 1 Product Details


Live Product Chat US Only
 8:30am - 5pm ET, Mon - Fri

1 - 86427 - 1
 [Active](#)

.100 AMPMODU Headers, Housings & Contacts

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Housing
- ? Not Preloaded
- ? Number of Positions = 3
- ? Housing Type = Receptacle
- ? Number of Rows = Single

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CONNECTOR HOUSING, CRIMP SNAP -IN MOD IV, SINGLE ROW,....](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Interconnection System, AMPMODU Mod IV 1/2](#) (PDF, English)

Application Specifications:

- ? [AMPMODU MOD IV, IV1/2, and V Receptacles and Housings](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Housing
- ? [Number of Positions](#) = 3
- ? [Mating Connector Lock](#) = Without
- ? [Strain Relief](#) = Without
- ? Mating Polarization = Without
- ? [Keyed](#) = No
- ? [Connector Series](#) = Mod IV
- ? Wire Termination Type = Crimp
- ? Stamped = Yes
- ? Flame Retardant = Yes
- ? Housing Configuration = Both Ends Closed
- ? Comment = Cavity identification, AMP, part number and date code stamped on housing where size permits.; Strain reliefs are available and may be purchased separately.

Mechanical Attachment:

- ? Preloaded = No

Body Related Features:

- ? [Housing Type](#) = Receptacle
- ? [Number of Rows](#) = Single
- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 [.100]

Housing Related Features:

- ? [Housing Color](#) = Black
- ? Housing Material = Thermoplastic

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP