



**TE CONNECTIVITY (TE)**  
**2X2 PLG ASY KEY A C3**  
 AMP | Sealed Sensor Connector (SSC) System

184344-1  
 TE Internal Number: 184344-1

Always EU RoHS/ELV Compliant  
 Connector Style **Housing for female terminals**

Number of Positions **4**

Pitch **5 mm [ .197 in ]**

Sealed **Yes**

Hybrid Connector **No**

[> See All Features](#)

Active

[PRODUCT DRAWING](#)  
English

[3D PDF](#)

[> See All Documentation](#)

Feedback

North America

GET SAMPLE



SAVE TO LIST



Contact us to request pricing, availability and customization options.

<a href="#">About TE Connectivity</a>	<a href="#">For Partners</a>	<a href="#">Customer Support</a>	<a href="#">CALL US</a>	<a href="#">LIVE CHAT</a>	<a href="#">United States</a>
<a href="#">Our Company</a> <a href="#">Events</a> <a href="#">TE News Center</a> <a href="#">Careers</a> <a href="#">Investors</a> <a href="#">Corporate Responsibility</a> <a href="#">Terms and Conditions of Sale</a>	<a href="#">Distributors</a> <a href="#">Suppliers</a>	<a href="#">Call</a> <a href="#">Email</a> <a href="#">Find Authorized Distributors</a> <a href="#">Access Product Tools &amp; Resources</a> <a href="#">Share Feedback</a>	     		

[PDF \(TIFF AVAILABLE\)](#)  
English

## CAD Files

[Customer View Model](#)

3D\_IGS.ZIP  
English

[Customer View Model](#)

3D\_STR.ZIP  
English

[Customer View Model](#)

2D\_DXF.ZIP  
English

[3D PDF](#)

PDF  
English

## Product Specifications

Product Specification

[Sealed Sensor Connector System](#)

PDF  
English

Qualification Test Report

[Sealed Sensor Connector System](#)

PDF  
English

## COMPATIBLE

Products - 12 Results

[View All](#)

[Compare 0/10](#)

Relation Type

### RELATIONSHIP

#### Seals

Used to identify Sealing Components

[See All Seals](#)

PRODUCT - SEALS



Connectors - Seals & Cavity Plugs  
 AMP | Sealed Sensor Connector (SSC) System

**WIRE SEAL, RUBBER, SENSOR, ORANGE - 184140-1**

TE INTERNAL NUMBER: 184140-1

Active

Always EU RoHS/ELV Compliant

Seal Type **Single Wire Seal (SWS)**

Cavity Diameter **4.4 mm**

Cable Insulation Diameter **1.6 – 2.1 mm**

Material **Silicone**

Resistance to Hydrocarbons

**POOR**

[Quick View](#)

### RELATIONSHIP

#### Seals

Used to identify Sealing Components

[See All Seals](#)

PRODUCT - SEALS



Connectors - Seals & Cavity Plugs  
 AMP | Sealed Sensor Connector (SSC) System

**WIRE SEAL, RUBBER, SENSOR, BLUE - 184139-1**

TE INTERNAL NUMBER: 184139-1

Active

Always EU RoHS/ELV Compliant

Seal Type **Single Wire Seal (SWS)**

Cavity Diameter **4.4 mm**

Cable Insulation Diameter **1.2 – 1.7 mm**

Material **Silicone**

Resistance to Hydrocarbons

**POOR**

[Quick View](#)

### RELATIONSHIP

#### Mating Products

Used to identify Mating Parts

[See All Mating Products](#)

PRODUCT - MATING PRODUCTS



Connectors - Automotive, Truck, Bus, & Off-Road Housings  
 AMP | Sealed Sensor Connector (SSC) System

**2X2 CAP ASY KEY A C3 - 184346-1**

TE INTERNAL NUMBER: 184346-1

Active

Always EU RoHS/ELV Compliant

Connector Style **Housing for male terminals**

Number of Positions **4**

Pitch **5 mm**

Sealed **No**

Hybrid Connector **No**

[Quick View](#)