


2057085-4 Product Details

Share | Print | Email



2057085-4

TE Internal Number: 2057085-4

Active

View 3D PDF

Pluggable Connectors, Cages & Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- SFP+ Enhanced Application
- Cage
- Cage Type = Single
- EMI Containment = Elastomeric Gasket
- Heat Sink Application = Yes

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • SFP+ EHHANCED CAGE ASSEMBLY PRESS FIT, EMI GASKET, W... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • Single Port SFP+ Cages, Ganged SFP+ Cages, and SFP+ ... (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • Small Form-Factor Pluggable (SFP) and SFP+ Surface Mo... (PDF, English) <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version A) • 3D Model (IGES, Version A) • 3D Model (STEP, Version A) 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Cage • Termination Type = Press-Fit <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Configuration = Single Port • PCB Mount = Single Sided <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Heat Sink Type = Networking, Hard Coat Anodized <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Post Length (mm [in]) = 2.05 [0.081] <p>Dimensions:</p> <ul style="list-style-type: none"> • Length (mm [in]) = 49.15 [1.935] • Width (mm [in]) = 14.00 [0.551] • Height (mm [in]) = 22.80 [0.898] <p>Housing Features:</p> <ul style="list-style-type: none"> • Cage Type = Single • Cage Material = Nickel Silver 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • EMI Containment = Elastomeric Gasket • Lightpipe = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = SFP+ Enhanced • Heat Sink Application = Yes <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Box <p>Other:</p> <ul style="list-style-type: none"> • Brand = Tyco Electronics

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

