



2143307-1 Product Details

Share Print Email



2143307-1

TE Internal Number: 2143307-1



Pluggable Connectors, Cages & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- QSFP+ Product Line
- Cage Assembly
- QSFP+ Application
- Cage Type = Ganged
- For Use With QSFP SMT Connector

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Feedback

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • 1X6 CAGE ASSEMBLY, BEHIND BEZEL, W/ LIGHT PIPES AND ... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Line = QSFP+ • Product Type = Cage Assembly • Heat Sink Type = PCI • Heat Sink Style = Pin <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • PCB Mount = Double Sided (Belly-to-Belly) • Bezel Mounting Style = Behind Bezel <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Data Signal Rate (Gb/s) = Up to 64 <p>Termination Features:</p> <ul style="list-style-type: none"> • Termination Method to PC Board = Press-Fit <p>Body Features:</p> <ul style="list-style-type: none"> • Heat Sink Finish = Nickel <p>Housing Features:</p> <ul style="list-style-type: none"> • Cage Type = Ganged 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Port Configuration = 1x6 • Heat Sink Included = Yes • Lightpipe = With • Lightpipe Configuration = Dual, Round • EMI Containment = Internal Springs <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • For Use With = QSFP SMT Connector • Applies To = Printed Circuit Board <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = QSFP+ • Heat Sink Application = Yes <p>Other:</p> <ul style="list-style-type: none"> • Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

