

2057162-1 Product Details

[Share](#) [Print](#) [Email](#)



2057162-1

TE Internal Number: 2057162-1

Active

[View 3D PDF](#)

Pluggable Connectors, Cages & Accessories

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- SFP+ Enhanced Application
- Cage
- Cage Type = Ganged
- EMI Containment = Elastomeric Gasket
- Heat Sink Application = No

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SFP+ ENHANCED, 1X4 CAGE ASSEMBLY PRESS FIT, EMI GASKET \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Single Port SFP+ Cages, Ganged SFP+ Cages, and SFP+ ... \(PDF, English\)](#)

Application Specifications:

- [Small Form-Factor Pluggable \(SFP\) and SFP+ Surface Mo... \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Cage
- [Termination Type](#) = Press-Fit

Mechanical Attachment:

- [Configuration](#) = 1 x 4
- PCB Mount = Single Sided

Termination Features:

- Termination Post Length (mm [in]) = 2.05 [0.081]

Dimensions:

- Height (mm [in]) = 9.70 [0.382]

Body Features:

- Length (mm [in]) = 48.70 [1.917]
- Width (mm [in]) = 57.25 [2.254]

Housing Features:

- [Cage Type](#) = Ganged
- Cage Material = Nickel Silver

Configuration Features:

- EMI Containment = Elastomeric Gasket
- Lightpipe = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- [Application](#) = SFP+ Enhanced
- Heat Sink Application = No

Packaging Features:

- Packaging Method = Box

Other:

- Brand = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

