

HOOD KIT MOTORMAN HC 180 PLAST

✓ ACTIVE

MotorMan

TE Part # **2120451-1**

TE Internal #: **2120451-1**

Connector System : **Cable-to-Panel**

Insertion Force : **7 kg**

Housing Material : **PBT GF15**

Connector Style : **Assembly Module**

Sealable : **Yes**

Add to List ▾

[Similar Products](#)



ORDER SAMPLES

Compatible Parts & Tooling



SHOP OUR DISTRIBUTORS (4)

North America ▾

Distributor	Phone Number	Buy
DIGI-KEY ELECTRONICS 72 in stock	1-800-344-4539	Visit Site
MOUSER ELECTRONICS 72 in stock	(800) 346-6873	Visit Site
HEILIND ELECTRONICS 72 in stock	1-800-400-7041	Visit Site

VIEW ALL DISTRIBUTORS

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

HOOD KIT MOTORMAN HC 180 PLAST

[HOOD KIT MOTORMAN HC 180 PLAST](#) English

CAD Files

3D PDF

[3D_CVM_CVM_2120451-1_C.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_2120451-1_C.2d_dxf.zip](#)

English

[ENG_CVM_CVM_2120451-1_C.3d_igs.zip](#)

English

[ENG_CVM_CVM_2120451-1_C.3d_stp.zip](#)

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System : **Cable-to-Panel**

Insertion Force : **7 kg**

Connector Style : **Assembly Module**

Sealable : **Yes**

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US




CALL US

Contact Features	Contact Current Rating (Max) (A): 20
Mechanical Attachment	Connector Mounting Type : Motor
Housing Features	Housing Material : PBT GF15
Usage Conditions	Operating Temperature Range : -40 – 85 °C [-40 – 185 °F]
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

[> Contact Product Support](#)

Also in the Series | [MotorMan](#)



Circular Connector
Caps & Covers (1)



Circular Connector
Contact Inserts (2)



Circular Connector
Seals (1)



Rectangular
Backshells & Clamps
(3)

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

CALL US

LIVE CHAT

[United States](#)

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)

[Investors](#)

[Corporate Responsibility](#)

[Terms and Conditions of Sale](#)

[Distributors](#)

[Suppliers](#)

 [Email or Call Us](#)

 [Find Authorized Distributors](#)

 [What's New on TE.com](#)

 [Product FAQs](#)

[Select Country & Language](#)

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#) ▼

