


## 42663 -2 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**42663 -2**

[Active](#)

### Multiple Circuit Housings with Tabs & Receptacles Including FASTIN -FASTON

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Receptacle
- ? Tab Fit = 7.92 x 0.81 mm
- ? Wire Range = 1.25 -3.00<sup>2</sup> [16-12] mm [AWG]
- ? Insulation Diameter = 4.06 [.160] Max. mm [in]
- ? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [receptacle, fastin -faston, 7.92 \[.312\] series](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [FASTIN-FASTON 110, 187, 205 And 312 Series Receptacl...](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 7.92 x 0.81 [.312 x .032]
- ? [Insulation Diameter \(mm \[in\]\)](#) = 4.06 [.160] Max.
- ? [Receptacle Style](#) = Straight
- ? [Wire/Cable Type](#) = Regular Wire
- ? [Finish](#) = Tin
- ? [Material](#) = Brass
- ? [Insertion Force](#) = Normal
- ? [Insulation Support](#) = With
- ? [Crimp Type](#) = "F"
- ? FASTON = Yes
- ? For Housing Type = Multiple

#### Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 1.25 -3.00<sup>2</sup> [16-12]

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? [Packaging Method](#) = Strip

#### Other:

- ? Line = FASTIN -FASTON .312
- ? Brand = AMP