


5120795 -1 Product Details

Live Product Chat US Only
 8:30am - 5pm ET, Mon - Fri



5120795 -1

[Active](#)

2mm Hard Metric PCB Connectors and Accessories (Z -PACK HS3)

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Receptacle Assembly
- ? PCB Mount Angle = Right Angle
- ? Module Type = Left
- ? Number of Rows = 10
- ? Number of Positions = 50

[View all Features](#) |
 [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(6\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE ASSEMBLY, 50 POSITION, UNIVERSAL GUIDE PI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Z-PACK HS3 Dual Beam Connector System](#) (PDF, English)

Application Specifications:

- ? [Z-PACK HS3 6 - and 10 -Row Connectors](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version O1)
- ? [3D Model](#) (IGES, Version O1)
- ? [3D Model](#) (STEP, Version O1)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(6\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Receptacle Assembly
- ? [PCB Mount Angle](#) = Right Angle
- ? [Number of Positions](#) = 50
- ? Post Type = Compliant Post

Mechanical Attachment:

- ? [Module Type](#) = Left

Termination Related Features:

- ? Solder Tail Contact Plating = Tin over Nickel
- ? Termination (Solder) Post Length (mm [in]) = 2.27 [0.089]

Body Related Features:

- ? [Number of Rows](#) = 10

Contact Related Features:

- ? [Contact Style](#) = Short Tail
- ? [Guide Pin Style](#) = Universal Power Module
- ? Contact Material = Copper Alloy
- ? Contact Mating Area Plating = Gold over Nickel

Housing Related Features:

- ? Housing Material = Polyester GF

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP