


## 66555-3 Product Details

[Live Product Chat](#)



**66555-3**

TE Part Number: 66555-3

[Active](#)

[Add to Part List](#)

### CR ZIF Connector System

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

#### Product Highlights:

- Contact
- Contact Type = Crimp
- Wire Size = 0.08-0.2<sup>2</sup> [28-24] mm<sup>2</sup> [AWG]
- Loose Piece

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [ACTIVE CONTACT STRIP](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [CR Series Standard Zero-Entry-Force 120-Position Con...](#) (PDF, English)
- [Application and Maintenance for Hand Crimping Tool](#) (PDF, English)
- [AMP\\* CR SERIES ZERO-ENTRY-FORCE 156-POSITION CONNECTOR](#) (PDF, English)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Contact
- [Wire Size \(mm<sup>2</sup> \[AWG\]\)](#) = 0.08-0.2<sup>2</sup> [28-24]
- Wire Insulation Diameter (mm [in]) = 1.25 [0.049]
- Comment = Contact Plating is gold per MIL-G-45204 over nickel plate per QQ-N-290

#### Contact Related Features:

- [Contact Type](#) = Crimp
- Contact Material = Copper Alloy
- Contact Mating Area Plating Material = Gold over Nickel

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Loose Piece

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)