


## 926209 -8 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**926209 -8**

TE Part Number: 926209 -8

[Active](#)

[Add to Part List](#)

### .100 AMPMODU Headers, Housings & Contacts

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Housing
- ? Not Preloaded
- ? Number of Positions = 16
- ? Housing Type = Receptacle
- ? Number of Rows = Dual

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [2 X 1 BIS 2 X 15 POLIGES LOCKING CLIP GEHAUSE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files: ( [CAD Format & Compression Information](#) )

- ? [2D Drawing](#) (DXF, Version G)
- ? [3D Model](#) (IGES, Version G)
- ? [3D Model](#) (STEP, Version G)

[List all Documents](#)

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Product Type = Housing
- ? [Number of Positions](#) = 16
- ? [Mating Connector Lock](#) = Without
- ? Mating Polarization = Without
- ? [Keyed](#) = No
- ? [Connector Series](#) = Locking Clip
- ? Wire Termination Type = Crimp
- ? Stamped = No
- ? Housing Configuration = Both Ends Closed

#### Mechanical Attachment:

- ? Preloaded = No

#### Body Related Features:

- ? [Housing Type](#) = Receptacle
- ? [Number of Rows](#) = Dual
- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]

#### Housing Related Features:

- ? [Housing Color](#) = Black
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Material = PBT - GF

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- ? Brand = AMP