




# CONNECTOR HOUSINGS



TE CONNECTIVITY (TE)  
**SMP CONN. REC HSG 4P**  
Power-Signal Double Lock | 2.5mm Signal Double Lock

917794-1  
TE Internal Number: 917794-1

Always EU RoHS/ELV Compliant  
Connector System **Wire-to-Board**

Number of Positions **4**

Number of Rows **1**

Housing Material **Nylon 66**

Connector Style **Receptacle**

✓ Active

↓ 3D PDF

## CAD Files

### 3D PDF

PDF  
**3D**

### Customer View Model

2D\_DXF.ZIP  
**English**

### Customer View Model

3D\_IGS.ZIP  
**English**

### Customer View Model

3D\_STP.ZIP  
**English**

## Product Specifications

Product Specification

### SMP CONNECTOR

TIF  
**English**

### SMP CONNECTOR

PDF  
**English**

Application Specification

### Conditions Of 2.5mm Signal Double Lock Contacts

PDF  
**English**

### Conditions Of 2.5mm Signal Double Lock Contacts

TIF  
**English**

Please review product documents or [contact us](#) for the latest agency approval information.

	Connector Style	<b>Receptacle</b>
	Sealed	<b>No</b>
	Product Type	<b>Connector</b>
	Connector Type	<b>Housing</b>
	Applies To	<b>Printed Circuit Board</b>
<hr/>		
Configuration Features	Number of Positions	<b>4</b>
	Number of Rows	<b>1</b>
	Selectively Loaded	<b>No</b>
	Preloaded	<b>No</b>
<hr/>		
Electrical Characteristics	Operating Voltage (VAC)	<b>250</b>
<hr/>		
Body Features	Sealable	<b>No</b>
<hr/>		
Contact Features	Contact Type	<b>Tab</b>
	Shunts/Shorting Bars	<b>Without</b>
	Multiple Contact Types	<b>Without</b>
<hr/>		
Mechanical Attachment	Contact Retention	<b>Without</b>
<hr/>		
Housing Features	Housing Material	<b>Nylon 66</b>
	Housing Color	<b>Black</b>
<hr/>		
Operation/Application	Assembly Integration Feature	<b>Without</b>
<hr/>		
Identification Marking	Circuit Identification Feature	<b>Without</b>
<hr/>		
Packaging Features	Packaging Quantity	<b>500</b>
	Packaging Method	<b>Bag</b>
<hr/>		
Product Compliance	<a href="#">Statement of Compliance</a> PDF  <a href="#">VIEW ALL PRODUCT COMPLIANCE</a>	