

## 1106419-7 Product Details



**1106419-7**

TE Internal Number: 1106419-7

 **Active**

 [View 3D PDF](#)

### HTS Connectors and Accessories

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- HB Series
- Accessory
- Accessory Type = Hood
- Product Size = 3
- Dimensions (L x H x W) = 60.00 x 48.00 x 43.00 mm

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [HOOD HB6 \(PDF, English\)](#)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- None Available

##### Instruction Sheets:

- None Available

##### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing \(DXF, Version A11\)](#)
- [3D Model \(IGES, Version A11\)](#)
- [3D Model \(STEP, Version A11\)](#)

[List all Documents](#)

##### Additional Information:

- [Product Line Information](#)

##### Related Products:

- [Tooling](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Type = Accessory
- Accessory Type = Hood
- [Thread Size](#) = M25
- Material = Die Cast Aluminum
- Finish = Silver Gray

##### Electrical Characteristics:

- Product Size = 3

##### Body Related Features:

- Series = HB
- Dimensions (L x H x W) (mm [in]) = 60.00 x 48.00 x 43.00 [2.362 x 1.890 x 1.693]
- Entry Style = Side

##### Contact Related Features:

- Corrosion Protected = No

##### Configuration Related Features:

- Locking Device Type = Side Clip at Housing Bottom

##### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Packaging Related Features:

- Packaging Method = Loose Piece
- Packaging Quantity = 5

##### Other:

- Brand = HTS

 [BOOKMARK](#) 

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

#### Follow Us On:



#### Visit Us On:

