


## 1825152-4 Product Details



1825152-4

TE Internal Number: 1825152-4



[Search for Replacement Parts](#)

### DIP & SIP Switches - Standard

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Switch
- Switch Type = SIP
- PCB Mount Style = Through Hole
- Actuator Style = Slide
- Sealed

[View all Features](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Switch
- PCB Mount Style = Through Hole
- [Actuator Style](#) = Slide
- Sealed = Yes
- [Number of Switches](#) = 8
- Mount Angle = Vertical

#### Termination Related Features:

- Seal Type = Process

#### Body Related Features:

- Switch Type = SIP
- Series = S
- Centerline (mm [in]) = 2.54 [0.100]
- Height (mm [in]) = 5.00 [0.197]
- Length (mm [in]) = 22.80 [0.898]

#### Contact Related Features:

- Auto-Insertable = No
- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold Flash

#### Housing Related Features:

- Low Profile = Yes
- Housing Color = Black
- Housing Material = PPS
- UL Flammability Rating = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = Alcoswitch



### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

