


# 1-1520237-1 Product Details

[Share](#) [Print](#) [Email](#)


**1-1520237-1**  
(8910K207)

TE Internal Number: 1-1520237-1

 **Active**

 [View 3D PDF](#)

## Power Toggle Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

### Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 16.28 mm
- Toggle Style = Baton
- Bushing Length = 8.74 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [DIM'S FOR DBL. POLE TOOL HANDLE SW. FOR EUROPEAN USE](#) (PDF, English)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Termination Type = Screw-In Terminal

### Electrical Characteristics:

- UL/CSA 125V Current Rating (A) = 16
- UL/CSA 250V Current Rating (A) = 8
- UL/CSA 125V Horse Power Rating (hp) = 1.00

### Housing Features:

- Toggle Length (mm [in]) = 16.28 [0.641]
- Toggle Style = Baton

### Configuration Features:

- Bushing Length (mm [in]) = 8.74 [0.344]

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

### Other:

- Brand = Alcoswitch

## Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

## Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

## Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

## Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

