



368084-1 Product Details



368084-1

TE Internal Number: 368084-1

 **Active**

 [View 3D PDF](#)

MULTILOCK Connectors and Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact
- Contact Type = Receptacle
- Applies To Wire
- Wire/Cable Type = Discrete Wire
- Wire Range = 0.80-1.40² [18-16] mm [AWG]

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [.090 II MLC RECEPTACLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version K)
- [3D Model](#) (IGES, Version K)
- [3D Model](#) (STEP, Version K)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Contact
- Wire/Cable Type = Discrete Wire
- Proprietary Name = MULTILOCK
- Product Series = .090 II

Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.80-1.40² [18-16]

Contact Related Features:

- Contact Type = Receptacle
- [Contact Base Material](#) = Copper Alloy
- [Contact Plating, Mating Area, Material](#) = Pre-Tin

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:


- [Applies To](#) = Wire
- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 1.40 - 2.50 [0.055 - 0.098]

Packaging Related Features:

- [Packaging Method](#) = Strip

Other:

- Brand = Tyco Electronics

 [BOOKMARK](#)   

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

