



## Industrial grade straight blade devices

### Product description

2-pole, 3-wire grounding  
20A, 125V/AC  
NEMA 5-20



6766

### Industrial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	125	5-20	Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5366	<input type="checkbox"/> AH5369	•	•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	BK	<input type="checkbox"/> AH5364BK	<input type="checkbox"/> AH5369BK	•	
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	Y	<input type="checkbox"/> AH5364Y	<input type="checkbox"/> AH5369Y	•	

### Industrial grade flanged inlets & outlets



Rating A	V/AC	NEMA	Description	Color	Inlet catalog no.	Outlet catalog no.		
20	125	5-20	Nylon construction, back wire	BK & W	<input type="checkbox"/> 5778C	<input type="checkbox"/> 5779C*	•	•

\* UL Listed only





5778C

## Industrial grade straight blade devices

### Product description

2-pole, 3-wire grounding  
15A, 250V/AC  
NEMA 6-15



AH5666Y

### Industrial grade plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	250	6-15	Ultra grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> AH5666 <sup>†</sup>	<input type="checkbox"/> AH5669 <sup>†</sup>	•	•
			Quick grip straight body	0.22-0.66" (5.6-16.7mm)	Y	<input type="checkbox"/> AH5666Y <sup>†</sup>	<input type="checkbox"/> AH5669Y <sup>†</sup>	•	
			Auto grip straight body	0.33-0.66" (8.3-16.7mm)	BK & W	<input type="checkbox"/> 5666N	<input type="checkbox"/> 5669N	•	•

<sup>†</sup> Not NOM Spec

### Industrial grade flanged inlets & outlets



Rating A	V/AC	NEMA	Description	Color	Inlet catalog no.	Outlet catalog no.		
15	250	6-15	Nylon construction, back wire	BK & W	<input type="checkbox"/> 5678C	<input type="checkbox"/> 5679C*	•	•

\* UL Listed only



5679C

**Industrial grade dimensional**  
Information: B-14-B15

**Specification Information:**  
Safety grip industrial plugs & connectors: B-22  
Quick grip plugs & connectors: B-22  
Auto grip industrial plugs & connectors: B-22  
Industrial flanged inlets & flanged outlets: B-23

### Color information:

BK (Black), W (White), Y (Yellow)



**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page Q-30

RoHS compliant - Page Q-30