


Hart-Lock™ Industrial Specification Grade Locking Devices


2-Pole, 3-Wire Grounding
30A, 277V/AC
NEMA L7-30




CWL730C



IGL730R



L730RW



CWL730FI

Dimensional Information: C-79 – C-82

Plug & Connector Specification Information:

- Safety Grip L7-30: C-88
- Severe Duty: C-97
- Watertight: C-95

Receptacle Specification Information:

- L7-30: C-91
- Isolated Ground L7-30: C-91
- Watertight: C-96

Flanged Inlet & Flanged Outlet Specification Information:

- L7-30: C-93

30A, 277V NEMA L7-30

Plugs & Connectors

Style & Description	Cord Dia.	Catalog No.		Certifications				
		Plug	Connector	USA	UL	UL	UL	UL
Safety Grip™ Straight Body, Black & White	0.38-1.00" (9.5-25.4mm)	<input type="checkbox"/> CWL730P	<input type="checkbox"/> CWL730C	•	•	•	•	•
Severe Duty, Yellow & Black	0.38-1.00" (9.5-25.4mm)	<input type="checkbox"/> L730PY	<input type="checkbox"/> L730CY	•			•	
Watertight, Yellow	0.43-1.15" (10.9-29.2mm)	<input type="checkbox"/> L730PW	<input type="checkbox"/> L730CW	•			•	
Watertight, All-Black	0.43-1.15" (10.9-29.2mm)	<input type="checkbox"/> L730PWBK	<input type="checkbox"/> L730CWBK	•			•	

Receptacles

Style & Description	Catalog No. Single Receptacle	Certifications				
		USA	UL	UL	UL	UL
Standard Industrial, Black	<input type="checkbox"/> CWL730R	•	•	•	•	•
Isolated Ground, Orange	<input type="checkbox"/> IGL730R	•	•			•
Watertight, Yellow	<input type="checkbox"/> L730RW	•		•		
Watertight, All-Black	<input type="checkbox"/> L730RWBK	•		•		

Flanged Inlets & Outlets

Style & Description	Catalog No.		Certifications				
	Flanged Inlet	Flanged Outlet	USA	UL	UL	UL	UL
Standard Industrial, Black & White	<input type="checkbox"/> CWL730FI	—	•	•	•		
Standard Industrial, Black & White	—	<input type="checkbox"/> CWL730FO	•	•			•

Icon Key

NAFTA Compliant - see page O-30

Accessories for NEMA L7-30 Locking Devices

Description	Catalog No.	USA
Neoprene weather protective boot for 30A plug	<input type="checkbox"/> BM1	•
Neoprene weather protective boot for 30A connector	<input type="checkbox"/> BM2	•
Closure cap for 30A Severe Duty plug and connector or watertight plug	<input type="checkbox"/> 30PW	•
Replacement closure cap for 30A watertight connector	<input type="checkbox"/> 30CW	•



BM1



BM2



30PW



30CW