

# Specifications

## Eaton IG8300W

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, White, Brass, High-impact nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Glass-filled nylon, Core pack

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart heavy-duty hospital grade duplex receptacle
<b>CATALOG NUMBER</b>	IG8300W
<b>UPC</b>	032664560446
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	0.89 in
<b>PRODUCT WEIGHT</b>	0.37 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL NOM Federal Specification Classification 6233 01



Powering Business Worldwide

## Product specifications

<b>DEVICE TYPE</b>	Receptacle
<b>TYPE</b>	Duplex receptacle
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	125V
<b>CONTACT MATERIAL</b>	Brass
<b>FEATURES</b>	Isolated ground Auto-grounding Terminal guards
<b>APPLICATION</b>	Healthcare
<b>DEVICE GRADE</b>	Heavy-duty hospital grade
<b>WIRING METHOD</b>	Back and side
<b>NUMBER OF WIRES</b>	3
<b>MOUNTING METHOD</b>	Flush
<b>NUMBER OF POLES</b>	Two-pole
<b>STYLE TYPE</b>	Standard
<b>MATERIAL</b>	Glass-filled nylon
<b>PACKAGING TYPE</b>	Core pack
<b>COLOR</b>	White
<b>CONNECTION TYPE</b>	Screw
<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>NEMA CONFIGURATION</b>	5-20R
<b>TORQUE RATING</b>	14 lbf-inch
<b>DESIGN TYPE</b>	Straight blade
<b>FACE/BODY MATERIAL</b>	High-impact nylon face Glass-filled nylon base
<b>RECEPTACLE TYPE</b>	Duplex

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Resources

<b>MULTIMEDIA</b>	<a href="#">Residential straight blade receptacles</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Arrow Hart extra heavy-duty hospital grade isolated ground straight blade receptacles</a> <a href="#">Eaton Specification Sheet - IG8300W</a>
<b>TECHNICAL DATA SHEETS</b>	<a href="#">Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles</a>



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

