

# Complete units: Pushbuttons $\phi$ 22MM

## ► SPRING RETURN - ILLUMINATED

 Technical Info (p. 106)


### TWIN TOUCH - FLUSH-FLUSH

Chrome Bezel  
Part Number

Black Bezel  
Part Number



L61QH21-3EAWM11



Center part illuminated - White LED Block (other colors available)


#### 12/24 VAC/DC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QH21-3EAWL11	L62QH21-3EAWL11

#### 12/24 VAC/DC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QH21A-3EAWL11	L62QH21A-3EAWL11

#### 130 VAC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QH21-3EAWM11	L62QH21-3EAWM11

#### 130 VAC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QH21A-3EAWM11	L62QH21A-3EAWM11

#### 230 VAC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QH21-3EAWH11	L62QH21-3EAWH11


#### 230 VAC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QH21A-3EAWH11	L62QH21A-3EAWH11

### TWIN TOUCH - FLUSH-PROJECTING





L61QK21A-3EAWL11



Center part illuminated - White LED Block (other colors available)

#### 12/24 VAC/DC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QK21-3EAWL11	L62QK21-3EAWL11

#### 12/24 VAC/DC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QK21A-3EAWL11	L62QK21A-3EAWL11

#### 130 VAC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QK21-3EAWM11	L62QK21-3EAWM11

#### 130 VAC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QK21A-3EAWM11	L62QK21A-3EAWM11

#### 230 VAC - WITH INTERNATIONAL SYMBOLS

	Green	NO		
	Red	NC	L61QK21-3EAWH11	L62QK21-3EAWH11

#### 230 VAC - WITH TEXT

	Green (START)	NO		
	Red (STOP)	NC	L61QK21A-3EAWH11	L62QK21A-3EAWH11