



Part Number: 8530

Lead Wire, #22 Sol TC, PVC Ins, TYPE MW MIL-W-76C-PVC 1000V 80C

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 22AWG (Solid) Tinned Copper, PVC Insulation, TYPE MW MIL-W-76C-PVC 1000V 80C

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	Solid	TC - Tinned Copper	1

Conductor Count: 1

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.059 in	0.017 in

Outer Jacket Material

Material
No Jacket

Electrical Characteristics

Voltage

Voltage Rating [V]
1000 V

Temperature Range

Non-UL Temp Rating: 80°C

Standards

UL AWM Style:	N/A
Military Specification:	MIL-W-76C

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL voltage rating:	N/A
--------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
8530 010100	Black	612825213109	100 ft	
8530 0101000	Black	612825213116	1,000 ft	P
8530 006100	Blue, Light	612825213048	100 ft	
8530 0061000	Blue, Light	612825213055	1,000 ft	P
8530 001100	Brown		100 ft	
8530 0081000	Gray	612825213079	1,000 ft	
8530 005100	Green, Dark	612825213024	100 ft	
8530 0051000	Green, Dark	612825213031	1,000 ft	P
8530 003100	Orange	612825212980	100 ft	
8530 0031000	Orange	612825212997	1,000 ft	P
8530 002100	Red	612825212966	100 ft	
8530 0021000	Red	612825212973	1,000 ft	C
8530 0071000	Violet	612825213062	1,000 ft	P
8530 009100	White	612825213086	100 ft	
8530 0091000	White	612825213093	1,000 ft	P
8530 004100	Yellow	612825213000	100 ft	
8530 0041000	Yellow	612825213017	1,000 ft	P

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.

History

Update and Revision:	Revision Number: 0.249 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.