

9926 Hook-up/Lead - UL AWM Styles 1007 and 1569

For more Information
please call

1-800-Belden1

**Description:**

Tinned copper conductor, PVC insulation. Rated 105°C, 300V. Rated 600V peak for electronic circuits, and internal wiring of electronic and electrical equipment.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
1	26	7x34	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)	Min. Avg. Wall (in.)
PVC - Polyvinyl Chloride	0.016	0.015

Overall Insulation**Overall Cable**

Overall Nominal Diameter: 0.051 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 1.900 lbs/1000 ft.

Max. Recommended Pulling Tension: 3.500 lbs.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

AWM Specification:	UL Style 1007 (300 V 80°C)
UL AWM Style:	UL Style 1007 (300 V 80°C), UL Style 1569 (300 V 105°C)
UL Rating:	300 V RMS, 80°C and 300 V, 105°C
CSA Rating:	300 V RMS, 105°C
CSA Type:	TRSR-64
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	VW-1
CSA Flame Test:	FT1

Plenum/Non-Plenum

9926 Hook-up/Lead - UL AWM Styles 1007 and 1569

Plenum (Y/N):

No

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9926 0011000	1,000 FT	3.000 LB	BROWN	P	26 STR PVC BRN
9926 002100	100 FT	0.300 LB	RED		26 STR PVC RED
9926 0021000	1,000 FT	3.000 LB	RED	P	26 STR PVC RED
9926 0031000	1,000 FT	3.000 LB	ORANGE	P	26 STR PVC ORG
9926 0041000	1,000 FT	3.000 LB	YELLOW	P	26 STR PVC YEL
9926 0051000	1,000 FT	3.000 LB	GREEN, DARK	P	26 STR PVC GRN
9926 0071000	1,000 FT	3.000 LB	VIOLET	P	26 STR PVC VIO
9926 0081000	1,000 FT	3.000 LB	GRAY	P	26 STR PVC GRY
9926 0091000	1,000 FT	3.000 LB	WHITE	P	26 STR PVC WHT
9926 010100	100 FT	0.300 LB	BLACK		26 STR PVC BLK
9926 0101000	1,000 FT	3.000 LB	BLACK	P	26 STR PVC BLK
9926 0131000	1,000 FT	3.000 LB	BLUE, DARK	P	26 STR PVC D. BLU

Notes:

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 5 Revision Date: 11-09-2010

© 2012 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.