



Product: [FX Ultra Frame LC Duplex](#)

FX Ultra Frame LC Duplex

Product Description

FX Ultra Frame LC Duplex. Available in several port counts.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Weight:	4.46 kg
Height:	1.5 m
Depth:	2.2

Temperature Range

Operating Temp Range:	-10 to 60°C
Storage Temp Range:	-10 to 75°C

Product Material

Materials

Description	Material	Color	Type
Frame	Plastic - UL94V-0	Black	
Front Connector Body	Plastic - UL94V-0		LC Duplex

Standards

EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

Additional Notes

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box (60/box)
Included Parts:	Dust Caps
Related Parts:	FiberExpress Ultra Patch panels, Pre-terminated MPO low loss cable assemblies

History

Variants

Item #	Connector Type	Port Count	Fiber Count
FFSU12LD	LC Duplex	12 Port	24
FFSU06LD	LC Duplex	6 Port	12
FF4U12LD	LC Duplex	12 Port	24
FF1U12LD	LC Duplex	12 Port	24
FFSU03LD	LC Duplex	3 Port	6
FF1U03LD	LC Duplex	3 Port	6
FF3U03LD	LC Duplex	3 Port	6

FF4U03LD	LC Duplex	3 Port	6
FF4U06LD	LC Duplex	6 Port	12

Update and Revision:	Revision Number: 0.48 Revision Date: 01-31-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.