

[Skip to content](#)

Search By: Part Number Text [Tips](#)




Sunday, April 30, 2006

[Sign In](#)

[Home](#) > [Products](#) > [By Type](#) > [Terminal Blocks & Strips](#) > [Product Feature Selector](#) > Product Details

Product Details for 6PCV-15



6PCV-15

Tyco Part Number: 7-1437653-1



[Superseded Search for Replacement Parts](#)

Barrier Strips, Barrier Strip Sockets

[Not Reviewed for ELV/RoHS Compliance](#)

Product Highlights:

- Barrier Strip
- Tri-Barrier Block Series
- Base Style = Raised
- 9.53 mm Centerline
- Number of Levels = Single

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- [Mounting Ears](#) = Without
- [Number of Circuits](#) = 15
- [Screw Material](#) = Steel
- UL Recognized = File No. E54800
- Comment = Do not order Screw and Captive Clamp in combination with other top hardware.

Mechanical Attachment:

- [Mounting Style](#) = Direct (All Positions Filled)
- [Screw Plating](#) = Bright Zinc/Chrome

Electrical Characteristics:

- [Base Style](#) = Raised
- [Number of Levels](#) = Single
- [End Barriers](#) = Without
- [Mounting Insert](#) = Without
- [Top Hardware](#) = Steel Clamp-plate Combo Head Screws
- Bracket = Without
- Screw Head Type = Slotted

Body Related Features:

- [Block Series](#) = Tri-Barrier
- [Centerline \(mm \[in\]\)](#) = 9.53 [0.375]
- [Number of Rows](#) = 1
- [Terminal Style](#) = Printed Circuit Pin 5.08 [.200]
- CSA File No. = LR30811

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Other:

- Brand = Buchanan

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Italiano](#) | [正體中文 \(繁體\) \(Chinese\)](#) | [中文 \(•体\) \(Simplified Chinese\)](#) | [日本語 \(Japanese\)](#)

Country Sites: [China](#) | [Japan](#)

© 2006 Tyco Electronics All Rights Reserved

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)