

[Search Only Products /](#)

Solid Numbers Wire Marker Card



Solid Numbers Wire Marker Card

Part Number:

WM-5-SC-PK

Material:

Cloth

Dimensions:

0.75 in H x 0.25 in W

UOM:

Pack of 25 Sheets

Color:

Black on White

ADD TO CART

1





[Add To Favorites](#)

PEOPLE ALSO VIEWED



OVERVIEW

B-500 Repositionable Vinyl Cloth wire markers from Brady® are perfect for your general wire marking needs.

- Card-mounted wire markers allow for quick, on-the-spot wire marking
- Brady B-500 Repositionable Vinyl Cloth holds tightly to surfaces but allows item to be repositioned with ease if necessary
- Excellent flexibility for wrapping around curved surfaces
- Withstands moderate heat, oil, water and dirt

SPECIFICATIONS

Material Number	B-500
Cards or Sheets per Pack	25
Catalog Page #	220
Dimensions	0.75 in H x 0.25 in W
UOM	Pack of 25 Sheets
Finish	Matte
Maximum Service Temperature °F	176 °F

Minimum Service Temperature °F	-40 °F
Product Number	112248
UPC	662820912804
Quantity per Card or Sheet	72
Thickness	0.0088 in
Adhesive Type	Repositionable Rubber
Applications	Cable & Wire Marking
Color	Black on White
Label/Media Format	Die-Cut on Cards
Label Properties	Repositionable Labels
Material	Cloth
Resistance Properties	Abrasion-Resistant, Corrosion-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant, Water-Resistant, Weather-Resistant
Serialization	No Serialization
Text Legend	5

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)


Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)

- [About](#)
- [Careers](#)
- [Investors](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [Terms of Use](#)
- [ISO Certificates](#)
- [Sites](#)
- [Distributor Portal](#)
- [International Sites](#)
- [Safety Services & Software](#)
- [Smart ID Brand Protection Solutions](#)

6555 W. Good Hope Rd. Milwaukee, WI 53223
 Phone: 888-250-3082
 Hours: 7am-6pm CT
 Monday - Thursday;
 Friday 7am-5pm CT

manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.