


Masking Tape Label Cards

[Overview](#) | [Specifications](#)



Product Highlights:

Color: Beige
 Material Number: B-540 ([View Technical Data Sheet](#))

Choose your options: [Reset Options](#)

1 Dimensions
 0.1875 IN DIA

2 UOM
 PACK OF 25 CARDS

[View All Options](#)
 Part Number: CMC-1875-PK

— +

[Add To Favorites](#)

Customers Also Bought



Overview

These circular, creped masking tape dots are designed for the quick application and clean removal necessary for efficient production line applications.

- Mounted on Blue Streak dispenser cards for easy handling and quick application
- Matte tan finish with a removable rubber based pressure sensitive adhesive
- Good conformability, good resistance to heat and moisture and removes cleanly from most surfaces without adhesive residue

Specifications

Key Characteristics	Product Number	150797
	UPC	754473629991
	UOM	Pack of 25 Cards
	Quantity per Card or Sheet	144
	Cards or Sheets per Pack	25
	Unit Price	\$0.01/Label
	Brand Name	Brady®
	Country of Origin ?	United States of America
	HTS Code (Harmonized Tariff Schedule) ?	4821.90.2000
	ECCN (Export Commodity Control Number) ?	EAR99

Dimensions	Dimensions	0.1875 in Dia
	Diameter	0.1875 in
	Thickness	0.0064 in


Material Characteristics	Material Number ?	B-540 (View Technical Data Sheet)
	Material ?	Crepe Paper
	Label Properties	Removable
	Adhesive Type	Removable Rubber
	Finish	Matte
	Color	Beige
	Resistance Properties	Heat-Resistant, Humidity-Resistant
	Service Temperature Range °F	-94 °F - 122 °F
	Minimum Service Temperature °F	-94 °F
	Maximum Service Temperature °F	122 °F
	Compatible Surface Types	General

Product Features	Applications ?	Circuit Board Labeling, Safety Identification
	Application ?	Circuit Board Labeling, Safety Identification
	Shape	Circle
	Label/Media Format	Card


Compliance	UNSPSC ?	55122002
------------	--------------------------	----------

You May Also Like


<




BMP71 BMP61 M611 TLS 2200 Repositionable Vinyl Cloth Wire and Cable Labels
Multiple Options Available
from **\$40.49**




1" Small Core Repositionable Vinyl Cloth Wire and Cable Labels
Multiple Options Available
from **\$82.99**



BMP51 BMP53 Dissolvable Paper Labels
MC-1500-403
\$50.99




BMP61 M611 Repositionable Vinyl Cloth Labels
M61-103-498
\$54.99




BMP41 BMP51 BMP53 Dissolvable Paper Labels
MC-750-403
\$30.39

>

Recently Viewed



Board Inspection Arrows
Multiple Options Available
\$64.99



2" Character Height Black on White Outdoor Numbers and Letters
Multiple Options Available
from **\$5.59**

Corporate

- [About](#)
- [Careers](#)
- [Investors](#)
- [Do Not Sell My Personal Info](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [ISO Certificates](#)

Other Brady Sites

- [Distributor Portal](#)
- [International Sites](#)
- [Brady Virtual Showroom](#)

Help

- [Contact Us](#)
- [Customer & Technical Support](#)
- [Resource Center](#)
- [Searchable Support Articles](#)
- [Certificate Request](#)
- [Website Feedback](#)

Contact

6555 W. Good Hope Rd
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7:00am–5:00pm CT
Monday–Friday

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2021 © Brady Worldwide, Inc.

Let's Chat