




Printer Labels / Bradyprinter PR Plus Printer Labels /

Cable and Harness Marking Tags



**Cable and Harness Marking Tags**

**Part Number:**

HSNX-800-2-YL-S

**Material:**

Nomex™

**For Use with Printer:**BradyPrinter i7100, BRADYPRINTER PR  
Plus Series Label Printer**Material Number:**

B-508

**Color:**

Yellow

**Quantity per Roll:**

250

[ADD TO CART](#)

1

[Add To Favorites](#)**PEOPLE ALSO VIEWED****OVERVIEW**

B-508 tags are designed as high performance bundle and cable identification tags to stand up to the harshest environments.

- Dot matrix or thermal transfer printable tags are available in white, yellow or green
- B-508 tags have excellent tear, solvent and heat resistance properties
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC
- Service temperature of -70°F to 130°F (-94°C to 266°C)

**SPECIFICATIONS**

Material Number	<b>B-508</b>
Dimensions	0.8 in H x 2.2 in W
UOM	Roll
Finish	Matte
Flame Retardant?	Yes
Maximum Service Temperature °F	266 °F
Minimum Service Temperature °F	-94 °F
Product Number	131569
UPC	662820999577
Quantity per Roll	250
Thickness	0.012 in
Web Width	3.25 in
Applications	Cable & Wire Marking
Color	Yellow
For Use with Printer	BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer
Material	Nomex™
Material Properties	Rigid
Resistance Properties	Chemical-Resistant, Corrosion-Resistant, Heat-Resistant, Humidity-Resistant, Tear-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R2000, R4300, R5000

## Solutions

[Floor Marking Guide](#)  
[GHS Label Compliance](#)  
[Lockout Tagout Compliance](#)  
[Arc Flash Labeling Requirements](#)  
[Cable and Wire Label Options](#)  
[Product and Barcode Labeling](#)  
[Brand Protection Solutions](#)

## Services

[Lockout Tagout Services](#)  
[Arc Flash Services](#)  
[Confined Space Services](#)  
[Visual Workplace Services](#)  
[Hazcom GHS Services](#)  
[Software Programming & Integration](#)  
[Label Template & File Conversion](#)  
[Printer Use & Training](#)  
[Printer Preventative Maintenance](#)  
[Toll and Custom Coating](#)  
[Authentication & Tracking Services](#)

## Help


[Contact Us](#)  
[Knowledge Center](#)  
[Printer Drivers & Firmware](#)  
[Brady Software Updates](#)  
[Safety Data Sheets](#)  
[Technical Data Sheets](#)  
[WEEE-RoHS Compliance](#)  
[Product Certification](#)  
[Printer Registration](#)

## Resources

[Find a Distributor](#)  
[Design Custom Safety Signs](#)  
[Printer Selection Tool](#)  
[Label Selection Tool](#)  
[Digital Catalog](#)  
[Request a Catalog](#)  
[Interactive Facility Map](#)  
[EPA e-Manifest Update](#)

**Corporate** **Other BradyContact**  
**Sites**  
**About** **6555 W.**  
**Careers** **Distributor** **Good Hope**  
**Investors** **Portal** **Rd.**  
**Privacy** **International** **Milwaukee,**  
**Policy** **Sites** **WI 53223**  
**Terms and** **Safety** **Phone: 888-**  
**Conditions** **Services &** **250-3082**  
**Terms of** **Software** **Hours: 7am-**  
**Use** **Smart ID** **6pm CT**  
**ISO** **Brand** **Monday -**  
**Certificates** **Protection** **Thursday;**  
**Solutions** **Friday 7am-**  
**5pm CT**

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 © Brady Worldwide, Inc.