


Labels / Wire and Cable Labels / Wire and Cable Label Cards /

Numbers and Letters Wire Markers



Numbers and Letters Wire Markers

Part Number:

WM-A1-PK

Dimensions:

1.5 in H

Material:

Cloth

Color:

Black on White

Text Legend:

A1

ADD TO CART

1



[Add To Favorites](#)

[Free sample pack](#)  [Download guide](#) 

PEOPLE ALSO VIEWED



OVERVIEW

B-500 Repositionable Vinyl Cloth wire markers from Brady® are perfect for your general wire marking needs.

- Card-mounted wire markers allow for quick, on-the-spot wire marking
- Brady B-500 Repositionable Vinyl Cloth holds tightly to surfaces but allows item to be repositioned with ease if necessary
- Excellent flexibility for wrapping around curved surfaces
- Withstands moderate heat, oil, water and dirt

SPECIFICATIONS

Material Number	B-500
Cards or Sheets per Pack	25

Dimensions	1.5 in H
UOM	Pack
Finish	Matte
Maximum Service Temperature °F	176 °F
Minimum Service Temperature °F	-40 °F
Product Number	112328
UPC	662820913603
Quantity per Card or Sheet	36
Thickness	0.0088 in
Adhesive Type	Repositionable Rubber
Applications	Cable & Wire Marking
Color	Black on White
Label/Media Format	Die-Cut on Cards
Material	Cloth
Resistance Properties	Abrasion-Resistant, Corrosion-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant, Water-Resistant, Weather-Resistant
Serialization	No Serialization
Text Legend	A1

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)

Brady
[About Sites](#) [Press](#) [Releases](#)
[Careers](#) [Request a](#)
[Investors](#) [Distributors](#)
[Privacy Policy](#) [International Sites](#)
[Terms and Conditions](#) [Safety Services](#)
[Terms of Use](#) [Software and Solutions](#)
[ISO Certification](#)

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.