


Labels / Wire and Cable Labels / Wire and Cable Self-lams and Wraps /
B33 Series Self-Laminating Vinyl Wire and Cable Labels



B33 Series Self-Laminating Vinyl Wire and Cable Labels

Part Number:

B33-73-427

Label/Tape Size (in/ft/yd):

1.750 in H x 0.75 in W

[ADD TO CART](#)

1

[Free sample pack](#)  [Download guide](#) 

OVERVIEW

Self-Laminating Vinyl (B-427) is an excellent material for wire and cable identification. This material has good clarity, conformability and is self-extinguishing.

- Provided in a self-laminated format with a white printable zone and translucent overlaminating area to protect text
- Durable, permanent acrylic adhesive has outstanding water and oil resistance
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved
- Service temperature of -40°F to 158°F (-40°C to 70°C)

SPECIFICATIONS

Brady Material Number	B-427
Dimensions	1.750 in H x 0.75 in W
Display UoM	Roll of 3500 Labels
Horizontal Repeat	0.8 in
Label/Tape Size (in/ft/yd)	1.750 in H x 0.75 in W
Maximum Service Temperature °F	158 °F
Maximum Wire Diameter (in/ft/yd)	0.40 in
Minimum Service Temperature °F	-40 °F
Minimum Wire Diameter (in/ft/yd)	0.2 in
Overlaminated Included	Overlaminated Included
Pre-Printed Areas on Label	Colored Write-On Area

Printable Area Dimensions	0.5 in H x 0.75 in W
Printable Area Height (in/ft/yd)	0.5 in
Printable Area Width (in/ft/yd)	0.75 in
Product Number	143008
UPC	662820968481
Quantity per Roll	3500
Quantity per Row	4
Thickness (in/ft/yd)	0.004 in
Trade Name	BBP®33
Vertical Repeat	1.874 in
Web Width (in/ft/yd)	3.35 in
Adhesive Type	Permanent Acrylic
Applications	Cable & Wire Marking
Color	Clear/White
For Use with Printer	BBP®33 Label Printer
Header	No Header
Label/Media Format	Roll
Material	Vinyl
Material Properties	Self-Extinguishing, Self-Laminating
Print Technology	Thermal Transfer
Resistance Properties	Chemical-Resistant, Humidity-Resistant, Oil-Resistant, Water-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4300

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)



Brady
 (NYSE:BRC)
 is a
 manufacturer
 of complete
 solutions
 that
 identify and
 protect
 people,
 products
 and places.
 Brady's
 products
 help
 customers
 increase
 safety,
 security,
 productivity
 and
 performance
 and include
 high-
 performance
 labels,
 signs, safety
 devices,
 printing
 systems
 and
 software.

Contact About

6555
 W.
 Good
 Hope
 Rd.
 Milwaukee,
 WI
 53223
 Phone:
 888-
 250-
 3082
 Hours:
 7am-
 6pm
 CST
 Monday
 -
 Friday

- [Corporation](#)
- [Privacy](#)
- [Policy](#)
- [Terms](#)
- [and](#)
- [Conditions](#)
- [Terms](#)
- [of Use](#)

Other

- Brady**
- Sites**
- Distribu**
- Portal**
- International**
- Sites**
- Safety**
- Services**
- &**
- Software**
- Smart**
- ID**
- Brand**
- Protection**



© 2017 Brady Worldwide, Inc.