


Printers and Scanners / Desktop Printers, Labels and Accessories / BBP33 Label Printer, Labels and Accessories / BBP33 Label Printer Labels /

B33 Series CleanLift Repositionable Vinyl Cloth Labels



# B33 Series CleanLift Repositionable Vinyl Cloth Labels

**Part Number:**

B33-87-498

**Label/Tape Size:**

1.437 in H x 0.5 in W

ADD TO CART

1

## PEOPLE ALSO VIEWED

## OVERVIEW

Permanent or repositionable: once applied, B-498 CleanLift® Series Vinyl Cloth is there to stay... unless you want to change it.

- The adhesive and cloth backing offers excellent holding power, yet allow for clean removal and repositioning
- Sticks to any clean, dry surface
- Specially formulated topcoat for excellent print quality
- Semi-gloss finish for crisp, clean look

## SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	<b>B-498</b>
Dimensions	1.437 in H x 0.5 in W
UOM	Roll of 2500 Labels
Horizontal Repeat	0.6 in
Indoor or Outdoor Use	N/A
Label/Tape Size	1.437 in H x 0.5 in W
Maximum Service Temperature °F	176 °F
Maximum Wire Diameter	0.46 in
Minimum Service Temperature °F	-40 °F
Minimum Wire Diameter	0.18 in

Pre-Printed Areas on Label	Colored Write-On Area
Printable Area Dimensions	0.5 in W
Printable Area Width	0.5 in
Product Number	143009
UPC	662820968498
Quantity per Roll	2500
Quantity per Row	6
Tamper Indication Type	N/A
Thickness	0.0073 in
Trade Name	BBP®33 CleanLift®
Vertical Repeat	1.563 in
Web Width	3.7 in
Adhesive Type	Repositionable Rubber
Applications	Cable & Wire Marking
Color	White
For Use with Printer	BBP®33 Label Printer
Header	No Header
Label/Media Format	Roll
Material	Cloth
Material Properties	N/A
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle
Suggested Ribbon Series	R6200



**B30 Series R6200 Printer Ribbon**

Part Number:  
B30-R6200

## Solutions

Floor Marking Guide  
GHS Label Compliance  
Lockout Tagout Compliance  
Arc Flash Labeling Requirements  
Cable and Wire Label Options  
Product and Barcode Labeling  
Brand Protection Solutions

## Services


Lockout Tagout Services  
Arc Flash Services  
Confined Space Services  
Visual Workplace Services  
Hazcom GHS Services  
Software Programming & Integration  
Label Template & File Conversion  
Printer Use & Training  
Printer Preventative Maintenance  
Toll and Custom Coating  
Authentication & Tracking Services

## Help

Contact Us  
Knowledge Center  
Printer Drivers & Firmware  
Brady Software Updates  
Safety Data Sheets  
Technical Data Sheets  
WEEE RoHS Compliance  
Product Certification  
Printer Registration

## Resources

Find a Distributor  
Printer Selection Tool  
Label Selection Tool  
Digital Catalog  
Request a Catalog



**Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.**

**Contact**  
6555 W. Good Hope Rd.  
Milwaukee, WI 53223  
Phone: 888-250-3082  
Hours: 7am-6pm CST  
Monday - Friday

**About**  
Brady Corporation  
Privacy Policy  
Terms and Conditions  
Terms of Use  
ISO Certificates

**Other**  
Brady Sites  
Distributor Portal  
International Sites  
Safety Services & Software  
Smart ID Brand Protection



2017 Brady Worldwide, Inc.