



[Labels](#) / [Labels by Application](#) / [Wire and Cable Labels](#) / [Wire and Cable Label Cards](#) /

HH-4-PK,B12,BLK/WHT,LEGEND: 4



# HH-4- PK,B12,BLK/WHT,LEGEND: 4

**Part Number:**

HH-4-PK

**Dimensions:**

1.5 in H

**Material:**

Cloth

**Text Legend:**

4

**Color:**

Black on White

[Free sample pack](#)  [Download guide](#) 

## OVERVIEW

Made of B-12 matte white acetate cloth, these HH series wire markers are oil and heat resistant making them perfect for withstanding varnish dip or baking cycles.

## SPECIFICATIONS

Material Number	<b>B-12</b>
Cards or Sheets per Pack	25
Catalog Page #	<a href="#">220</a>
Dimensions	1.5 in H
UOM	Pack of 25 Cards
Finish	Matte
Maximum Service Temperature °F	221 °F
Minimum Service Temperature °F	-40 °F
Product Number	111201
UPC	662820902331
Quantity per Card or Sheet	36
Thickness	0.008 in
Adhesive Type	Rubber
Applications	Cable & Wire Marking
Color	Black on White
Label/Media Format	Die-Cut on Cards
Label Properties	Harsh Environment Labels, Heat Resistant Labels, Permanent Adhesive Labels
Material	Cloth
Material Properties	Rigid
Resistance Properties	Corrosion-Resistant, Heat-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant
Serialization	No Serialization
Text Legend	4

## Solutions

Floor Marking Guide  
GHS Label Compliance  
Lockout Tagout Compliance  
Arc Flash Labeling Requirements  
Cable and Wire Label Options  
Product and Barcode Labeling  
Brand Protection Solutions

## Services

Lockout Tagout Services  
Arc Flash Services  
Confined Space Services  
Visual Workplace Services  
Hazcom GHS Services  
Software Programming & Integration  
Label Template & File Conversion  
Printer Use & Training  
Printer Preventative Maintenance  
Toll and Custom Coating  
Authentication & Tracking Services

## Help

Contact Us  
Knowledge Center  
Printer Drivers & Firmware  
Brady Software Updates  
Safety Data Sheets  
Technical Data Sheets  
WEEE-RoHS Compliance  
Product Certification  
Printer Registration

## Resources

Find a Distributor  
Digital Catalogue  
Request a Catalogue

<b>Corporate</b>	<b>Other Brady</b>	<b>Contact</b>
<a href="#">About</a>	<a href="#">Sites</a>	<b>710</b>
<a href="#">Careers</a>	<a href="#">Brady</a>	<b>Cochrane</b>
<a href="#">Investors</a>	<a href="#">Distributor</a>	<b>Drive,</b>
<a href="#">Privacy</a>	<a href="#">Portal</a>	<b>Markham</b>
<a href="#">Policy</a>	<a href="#">International</a>	<b>ON Canada</b>
<a href="#">Terms and</a>	<a href="#">Sites</a>	<b>L3R 5N7</b>
<a href="#">Conditions</a>	<a href="#">Safety</a>	<b>Phone: 1-</b>
<a href="#">Terms of</a>	<a href="#">Services &amp;</a>	<b>800-263-</b>
<a href="#">Use</a>	<a href="#">Software</a>	<b>6179</b>
<a href="#">ISO</a>	<a href="#">Smart ID</a>	<b>Fax: 1-800-</b>
<a href="#">Certificates</a>	<a href="#">Brand</a>	<b>387-4935</b>
	<a href="#">Protection</a>	<b>Hours:</b>
	<a href="#">Solutions</a>	<b>8:00am-</b>
		<b>5:30pm EST</b>
		<b>Monday -</b>
		<b>Friday</b>

**Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.**



2018 © Brady Worldwide, Inc.