




Labels / Wire and Cable Labels / Wire and Cable Label Cards /

Pre-printed B Wire Markers



## Pre-printed B Wire Markers

**Part Number:**

HH-B-PK

**Dimensions:**

1.5 in H

**Material:**

Cloth

**Color:**

Black on White

**Text Legend:**

B

**ADD TO CART**

1



[Add To Favorites](#)

[Free sample pack](#)  [Download guide](#) 

## PEOPLE ALSO VIEWED



## OVERVIEW

Made of B-12 matte white acetate cloth, these HH series wire markers are oil and heat resistant making them perfect for withstanding varnish dip or baking cycles.

## SPECIFICATIONS

Material Number	<b>B-12</b>
Cards or Sheets per Pack	25
Dimensions	1.5 in H
UOM	Pack
Finish	Matte

Maximum Service Temperature °F	221 °F
Minimum Service Temperature °F	-40 °F
Product Number	111209
UPC	662820902416
Quantity per Card or Sheet	36
Thickness	0.008 in
Adhesive Type	Rubber
Applications	Cable & Wire Marking
Color	Black on White
Label/Media Format	Die-Cut on Cards
Material	Cloth
Material Properties	Rigid
Resistance Properties	Corrosion-Resistant, Heat-Resistant, Humidity-Resistant, Oil-Resistant, UV-Resistant
Serialization	No Serialization
Text Legend	B

## Solutions

[Floor Marking Guide](#)  
[GHS Label Compliance](#)  
[Lockout Tagout Compliance](#)  
[Arc Flash Labeling Requirements](#)  
[Cable and Wire Label Options](#)  
[Product and Barcode Labeling](#)  
[Brand Protection Solutions](#)

## Services

[Lockout Tagout Services](#)  
[Arc Flash Services](#)  
[Confined Space Services](#)  
[Visual Workplace Services](#)  
[Hazcom GHS Services](#)  
[Software Programming & Integration](#)  
[Label Template & File Conversion](#)  
[Printer Use & Training](#)  
[Printer Preventative Maintenance](#)  
[Toll and Custom Coating](#)  
[Authentication & Tracking Services](#)

## Help

[Contact Us](#)  
[Knowledge Center](#)  
[Printer Drivers & Firmware](#)  
[Brady Software Updates](#)  
[Safety Data Sheets](#)  
[Technical Data Sheets](#)  
[WEEE-RoHS Compliance](#)  
[Product Certification](#)  
[Printer Registration](#)

## Resources

[Find a Distributor](#)  
[Printer Selection Tool](#)  
[Label Selection Tool](#)  
[Digital Catalog](#)  
[Request a Catalog](#)  
[Interactive Facility Map](#)

**Brady**  
[About Sites](#) [Press Releases](#)  
[Careers](#) [Request a Distributor](#)  
[Investors](#) [Portal](#) [a](#)  
[Privacy Policy](#) [International Sites](#) [Weblog](#)  
[Terms and Conditions](#) [Safety Services](#) [Find a Distributor](#) [Log Out](#)  
[Terms of Use](#) [Software and Solutions](#)  
[ISO Certification](#) [Smart ID Protection](#)

6555 W. Good Hope Rd. Milwaukee, WI 53223  
Phone: 888-250-3082  
Hours: 7am-6pm CT  
Monday - Thursday;  
Friday 7am-5pm CT

manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.